

MATERIALS AND FINISHES

BODY: STAINLESS STEEL
PLATED PASSIVATED

JAM NUT: BRASS
PLATED NICKEL

LOCKWASHER: PHOSPHOR BRONZE
PLATED NICKEL










CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD

CABLE CONTACT BRASS
PLATED GOLD

INSULATOR TEFLON

O RING SILICONE RUBBER

CRIMP USING .213 HEX DIE



RECOMMENDED MOUNTING HOLE PATTERN

RECOMMENDED CABLE STRIP

JAM NUT

LOCKWASHER

O RING

AS-89678-9400	CABLE ASSEMBLY INSTR.
PS-89675-1850	ELECTRO/MECH SPEC.
MIL-STD-348A, FIG. 321.1	INTERFACE
SPECIFICATION	DESCRIPTION

73298-0031	ONE PIECE 73298-0030 PER BAG
73298-0030	BULK
PART NO.	PACKAGING

CHG: CLARIFIED BAGGING. EC NO: URF2010-0369 DRWN:ROBERTSON 2009/12/18 CHKD:SSS 2009/12/18 APPR:JWIENER 2009/12/18 A2	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
		▽=0 ▽=0		mm	INCH	MM/IN			METRIC	
			4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE	BMA PLUG,STR,BLKHD FOR RG55,142,223,400,50 OHM EWR2216 BMA-PC	
			3 PLACES	± ---	± ---	TEF	2003/10/30			
			2 PLACES	± ---	± ---	CHECKED BY	DATE			
			1 PLACE	± ---	± ---	SSS	2003/11/04			
		ANGULAR ± 2 °			APPROVED BY	DATE				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			GMH	2003/11/04				
					MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
					SEE TABLE		SD-73298-003		1 OF 1	

SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
------	---