



Part Number : [2196531022](#)
Product Description : Micro-One Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, Tin (Sn) Plating, 2 Circuits, Black
Series Number : 219653
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2196531022_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	219653
Description	Micro-One Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, Tin (Sn) Plating, 2 Circuits, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	Micro-One-to-Pigtail
Product Name	Micro-One
Type	Discrete Wire Assembly
UPC	195842803442

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Polyamide
Net Weight	2.112/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Single Ended	Yes

Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1569
Wire Insulation Diameter	1.10-1.60mm
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-One Vertical Single Row Headers	<u>205971</u>
Micro-One Vertical Single Row Headers	<u>217063</u>
Micro-One Right-Angle Single Row Headers	<u>205972</u>
Micro-One Right-Angle Single Row Headers	<u>217064</u>