



Part Number : [191400093](#)
Product Description : Krimptite Spade Tongue
Terminal for 16-14 AWG Wire,Non-Insulated,
Stud Size 10
Series Number : 19140
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : B-127-10



Documents & Resources

Drawings
[191400093_sd.pdf](#)

3D Models and Design Files
[191400093_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
 - REACH SVHC
 - Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19140
Description	Krimptite Spade Tongue Terminal for 16-14 AWG Wire,Non-Insulated, Stud Size 10
Keyword	Spade Terminal, Spade Terminals
Product Name	Krimptite
Type	Spade
UPC	800755086027

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.853/g
Packaging Type	Carton
Stud Size	10 (M5)
Temperature Range - Operating	149°C
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16

Wire Size mm ²	1.00-2.50
---------------------------	-----------

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>