




Part Number : [190670072](#)
Product Description : NylaKrimp Funnel Entry
Ring Tongue Terminal for 6 AWG Wire, Stud
Size 1/4" (M6)
Series Number : 19067
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : E-960-14T



Documents & Resources

Drawings
[190670072_sd.pdf](#)

3D Models and Design Files
[190670072_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)
[PS-19902-016-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size 1/4" (M6)
Keyword	Ring Terminal, Ring Terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753066328

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	5.424/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/4" (M6)
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	10.87mm max.
Wire Size (AWG)	6

Application Tooling

Global

Description	Part Number
Crimp Dies for 6 AWG Insulkrimp and NylaKrimp Mylar Tape, use with Tape Crimp Module and TM-4000 Crimp Press	<u>190472040</u>
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880225</u>