




1. THIS PLUG IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
  2. MAX WIRE INSUL. TO BE USED WITH THIS PLUG IS .054 DIA.
  3. METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
  4. PACKAGE MARKED M 24308/4-331F
  5. THIS PLUG WILL ACCEPT SIZE 22 PIN CONTACT M 24308/13 OR AMP # 204370
- AMP PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- UL/CSA DESIGNATION MARKED IN THIS AREA.

|          |                                                                                                                      |          |
|----------|----------------------------------------------------------------------------------------------------------------------|----------|
| OBSOLETE | PHENOLIC, COLOR: BLACK                                                                                               | 204529-2 |
|          | POLYPHENYLENE SULFIDE (PPS) GST-40F PER MIL-M-24519 OR GLASS FILLED POLYESTER TPES013G30 PER ASTM D5927 COLOR, BLACK | 204529-1 |
|          | INSERT MATERIAL                                                                                                      | PART NO. |

|                                        |  |                               |                                                           |  |
|----------------------------------------|--|-------------------------------|-----------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>C.C.THOMAS<br>12-3-87  | Tyco Electronics Corporation<br>Harrisburg, PA 17105-3608 |  |
| DIMENSIONS:<br>INCHES                  |  | CHK<br>F.C. BALLEW<br>1-25-88 | NAME                                                      |  |
|                                        |  | APVD<br>DJM<br>1-25-88        | PRODUCT SPEC                                              |  |
|                                        |  |                               | APPLICATION SPEC                                          |  |
|                                        |  |                               | RESTRICTED TO                                             |  |
|                                        |  |                               | CUSTOMER DRAWING                                          |  |
| MATERIAL<br>SEE CALLOUTS               |  | WEIGHT<br>—                   | SIZE<br>A1                                                |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | FINISH<br>SEE CALLOUTS        | SCALE<br>4:1                                              |  |
| 0 PLC ± —                              |  |                               | SHEET<br>1 OF 1                                           |  |
| 1 PLC ± —                              |  |                               | REV<br>S                                                  |  |
| 2 PLC ± —                              |  |                               |                                                           |  |
| 3 PLC ± .005                           |  |                               |                                                           |  |
| 4 PLC ± —                              |  |                               |                                                           |  |
| ANGLES ± —                             |  |                               |                                                           |  |