

VOLTCRAFT

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

DSA-3100

Digital Oscilloscope 3-in-1

CE

Item no: 3393783

This product is a 3-in-1 spectrum analyzer, oscilloscope, and digital multimeter.
The maximum permissible input quantities must never be exceeded.



FEATURES

Oscilloscope + multimeter + spectrum analyzer, 3 in 1 // 3.5-inch high-resolution // 100MHz bandwidth // Max 500 MSa/s sample rate // Max 8K record length // 10,000wfms/s high refresh rate // USB Type-C interface

CONTENTS

USB Cable // Probe x 2 // Probe adjust // Multimeter test leads x 1 pair (red & black) // Carrying bag // Operating instructions

TECHNICAL DATA

Input	5 V/DC, 2 A via USB-C®
Rechargeable battery	Li-ion 2600 mAh x2 (3.7 V, 18650)
Protection class	III
Operating temperature	0 to +40 °C
Operating humidity	≤90 % RH (non-condensing)
Storage temperature	-20 to +60 °C
Storage humidity	≤90 % RH (non-condensing)

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3393783_V1_0625_en_ds 2197258891 I1/O1 en