Antec

CX600M ARGB

Dual Chamber Mid-Tower





PANORAMIC 270° VIEW

Standing out with full-view design on the seamless steel-tempered glass, CX600M ARGB's left and front panel offer an unobstructed view of your build, creating a stunning showcase for your components.

DUAL CHAMBER

Dual-chamber design ensures independent cooling for CPU/GPU on the left and PSU/Drives on the right.

Cooling for CPU/GPU

Cooling for PSU/Drives



VERTICAL COOLING WITH MASSIVE AIR INTAKE


A large amount of air is taken in through the mesh on bottom and side, facilitating heat dissipation and quietest hardware from overheating.



Right Side

PRE-INSTALLED 3 x 120mm ARGB FANS

Use the major case fan to daisy-chain the other two fans for ARGB sync and create your personal style.



FAN INSTALLATION

SUPPORT 2 X WATER COOLER

Support simultaneous installation of 360mm radiator on top and 240mm radiator on side.



I/O PANEL




UP TO 9 FANS SIMULTANEOUSLY



POWERFUL AIR COOLING COMPATIBILITY

Max. CPU Cooler Height: 160mm



COMPATIBILITY

Motherboard support	Micro-ATX , ITX	2.5"	2
CPU cooler max height	≤ 160mm	3.5" / 2.5" Drive Mounts	1
GPU max length	≤ 410mm	Power Supply max length	(Include cable) ≤ 240mm

SUPPORT LENGTHY RTX 40 SERIES GPU

Max GPU Length: 410mm

AMPLE CABLE MANAGEMENT SPACE

99mm of cable management space ensures your PC build looks neat.

DIMENSIONS

435 x 290 x 370mm (DWH)

SPECIFICATIONS

Main Spec

Motherboard Support	Micro-ATX , ITX
Form Factor	Mini Tower
Case Material	Steel + Glass
Side & Front Panel	4mm Tempered Glass
I/O Ports	Power, Reset, LED Control, USB 2.0 x 2 , USB 3.0 x 1 , MIC / HD-AUDIO

Compatibility & Clearances

CPU Cooler Max Height	≤ 160mm
GPU Max Length	≤ 410mm
Power Supply Max Length	(Include cable) ≤ 240mm
Cable Routing Space	≥ 99mm

Fan Support

Top	3 x 120mm / 2 x 140mm
Side	2 x 120mm / 2 x 140mm
Bottom	3 x 120mm
Rear	1 x 120mm

Radiator Support

Top	120/140/240/280/360mm
Side	120/140/240/280mm
Bottom	120/240/360mm
Rear	120mm

Expansion Slots

Standard	5

Drive Bays

2.5"	2
3.5"	1

Dimensions

Case Dimensions	435 x 290 x 370mm (DWH)
Box Dimensions	425 x 375 x 525mm (DWH)
Net Weight	5.9kg
Gross Weight	7.15kg

Accessories

Included Fans	2 x 120mm ARGB reverse fans on right side + 1 x 120mm ARGB fan in rear

General

Dust Filter	Top / Bottom
Warranty	1 year
UPC#	0-761345-10147-9

Antec