

Power cable (USB-C to USB-C) rc 1.5m white/silver E-mark IC, 100W 20V 5A/480Mbps

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.5m / 22#(65/0.08TC+500D)*2C+30# (11/0.08TC+250D)*4C+AL PVC Middle quilt knitted with 24 spindles plus chanting yarn
Maximum Load	100W
USB standard	USB2.0
Fast charge	PD/QC
Communication	30AWG/4C&22AWG/2C
Transmission speed	480Mbps
Weight	N.W.: 37g / pc
Packing bunch	Various [pcs] 10



Extension cable (USB-C to USB-C) rc 1.5m apple white

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.5 m / 2464 20AWG/20+28AWG/3C White PVC UL OD 4.5mm
Maximum Load	60W
USB standard	USB2.0
Fast charge	PD/QC
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 57g / pc
Packing bunch	Various [pcs] 10



Extension cable (USB-C to USB-C) rc 1.5m black

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.5 m / 2464 20AWG/20+28AWG/3C Black PVC UL OD 4.5mm
Maximum Load	60W
USB standard	USB2.0
Fast charge	PD/QC
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 57g / pc
Packing bunch	Various [pcs] 10



Extension cable (USB-A to USB-C) rc 1.0m or 1.5m black

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.5 m / OD 4.5/50 2464 20ANG/2C+28ANG/30 Black/IC inside
Maximum Load	60W
USB standard	USB2.0
Fast charge	QC
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 48g / pc
Packing bunch	Various [pcs] 10



Extension cable (USB-A to micro USB) rc 1.4m

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1.4m / 20AWG – round cable
Maximum Load	60W
USB standard	USB2.0
Fast charge	N/A
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 36g / pc
Packing bunch	Various [pcs] 10

**Extension cable (USB-A to mini USB) rc 1.4m black or 1.8m white**

Operating Temperature	0 ÷ 45[°C]
Length / cable type	1,4m or 1,8m / 20AWG – round cable
Maximum Load	60W
USB standard	USB2.0
Fast charge	N/A
Communication	26AWG
Transmission speed	480Mbps
Weight	N.W.: 37g / pc
Packing bunch	Various [pcs] 10

