

Features

- Double USB Type C Socket
- Interchangeable Plug Set for USA, Europe and UK
- Charging Current of up to 65 Watt
- 1 Year Warranty



Marks / Approvals



Specifications

MODEL No.	Voltage	Rated Load USB1 + USB2	Output Power USB1 + USB2	Rated Load USB1 or USB2	Output Power USB1 or USB2
XYPD65CC-ZUZ	5 V	3.0 A	15 W	3.0 A	15 W
	9 V	3.0 A	27 W	3.0 A	27 W
	12 V	2.5 A	30 W	3.0 A	36 W
	15 V	2.0 A	30 W	3.0 A	45 W
	20 V	1.5 A	30 W	3.25 A	65 W
INPUT	Voltage	AC 100 V – 240 V			
	Frequency	50 Hz / 60 Hz			
	Current (rms max)	1.8 A			
	No Load Power Consumption	< 0.3 W			
PROTECTION	Overcurrent	4.1 A max.			
	Overvoltage	150 %			
	Short Circuit	Auto Recovery			
	Leakage Current	0.25 mA			
	Dielectric Strength Hi-Pot	Primary to Secondary: 3000 VAC or 4242 VDC 10 mA 60s			
	Insulation Resistance	50 MΩ			
	IP Rating	IP20 (Indoor)			
	Input Surge Current	< 150 A			
OTHERS	Compatibility Protocol List	PD 3.0, PD 2.0, PPS, QC 4+, QC 3.0, QC 2.0, AFC, FCP, SCP, Apple 2.4, BC 1.2			
	Energy Efficiency Level	VI			
	Turn On Delay	3 s max.			
	Ripple & Noise	200 mV p-p			
Environment	Temperature	Operating: 0 °C to 25 °C; Storage: -40 °C to 80 °C			
	Humidity	Operating: 5 % RH to 100 % RH; Storage: 5 % RH to 90 % RH			
Connector	Output	Double USB Type C Connector			
	Input	Interchangeable AC Plugs (US foldable): EU / UK			
MTBF	30000 hours (Ref: MIL-HDBK-217F)				
EMI	EN 55032				
EMS	EN 61000-4-2; EN 61000-4-3; EN 61000-4-5				
Case Dimensions	53.5 mm x 53.5 mm x 28.6 mm				

