



OVER-EAR O400HA

Headphones with Bluetooth 5.3

Technical details

Colour:	Black, White, Rose, Blue	Input:	USB-C (5.0 V/DC 1.0 A)
Main features:	Hybrid Active Noise Cancelling (ANC) for optimized reduction of ambient noise Transparency Mode to let through ambient noise Music Mode for a balanced music enjoyment (Full sound reproduction) Passive Mode for faster transmission between output devices and buds	Driver diameter:	40 mm
		ANC:	~35 dB
		Impedance:	32 Ohm
		Packing unit:	6
Other properties:	6 hours playtime after 15 min. charging, can be used wired via a 3.5mm audio jack, high wearing comfort, adjustable size, foldable for compact transport, multipoint bluetooth		
Bluetooth version:	V 5.3		
Bluetooth range:	Up to 15 m (line of sight)		
Frequency range:	20 Hz - 20 KHz		
Supported Codec:	SBC		
Scope of delivery:	Over-Ear headphones O400HA, USB-C to USB-C cable, 1.5 m audio cable with 3.5 mm jack plug		
Dimensions:	165 x 75 x 195 mm		
Weight:	248 g		
Play time:	up to 75 hours		
Battery:	600 mAh		
Charging time:	~2 hours		

Product data

Colour	Article no	EAN
Black	3740400	4 034303 035458
White	3740402	4 034303 035489
Rose	3740403	4 034303 035519
Blue	3740405	4 034303 035540