

DATASHEET

IEC connector plug

Item No. 3399880

powered
by
RICH BAY

Overview



Nominal current	10 A
Total number of pins	2 + PE
Colour	Black (Red transparent switch with light)
Material	Thermoplastic
Connection	Type C CEE 7/16 plug 4.8 mm, Solder pins
Plug standard (IEC 60320)	C14
Nominal voltage	250 V/AC
Connector type	Plug, vertical mount
Product type	IEC connector
Operating temperature range	-10 to +80 °C
Panel thickness	3 mm
Contact resistance	<20 mΩ
Dimension (L x W x H)	50 x 30.5 x 30.5 mm

Technical data

