ARMY



Code: #2170 - #2171 - #2172

This brand new products stands out as a true military binocular in both its classical design and its remarkable specifications, which make it an ideal choice for every sportsman and professional that is looking for rugged and highly perfroming equipment that will never let him down.

Its **BAK-4 prisms** and **multi-coated** optics provide the most brilliant vision and the most outstanding light transmission, while its twist up eye guards and generous eye-relief make for a **comfortable viewing experience.**
Its whole body is encased in a **robust rubber armouring** for **additional protection** versus the extreme abuse that often occurs while on the field.







Specifications

- BAK-4 PRISMS
- CENTRAL FOCUSING
- EXTRA LARGE EYEPIECE
- WIDE ANGLE (8×42 and 10×50)
- MULTICOATED OPTICS
- RUBBER COVERED
- TWIST UP EYE GUARDS

Technical Data

#2170 KONUSARMY 8×42 W.A.
Magnification x objective: 8×42 W.A.
Field of view 1000m/1000yds: 140m/459ft
Exit pupil: 4.5mm
Weight: 845gr – 29.8oz
Tripod Adaptable: YES

#2171 KONUSARMY 7×50
Magnification x objective: 7×5
Field of view 1000m/1000yds 110m/361ft
Exit pupil: 6.7mm
Weight: 970gr – 34.2oz
Tripod Adaptable: YES

#2172 KONUSARMY 10×50 W.A.
Magnification x objective: 10×50 W.A.
Field of view 1000m/1000yds: 112m/367ft
Exit pupil: 4.7mm
Weight: 970gr – 34.2oz
Tripod Adaptable: YES