



UN38.3 测试概要

Test summary of UN38.3

电池或电池组说明 Description of cell or battery: 型号 Model No.: EF-DL-E10-4 名称 Name: 二次锂离子电池组 Rechargeable Li-ion Battery Pack 类型 Type: Lithium ion battery 额定值 Rating: 51.2V, 20Ah, 1024Wh 形状 Description: 近长方体 Almost cuboid 质量 Mass: Approx. 9.8kg	测试实验室名称及联系信息 Name and contact information of the test laboratory: 名称 深圳沃特检验集团有限公司 Name: Waltek Testing Group Co., Ltd. 地址 中国广东省东莞市厚街镇莞太路厚街段 77 号 Address: No. 77, Houjie Section, Guantai Road, Houjie Town, Dongguan City, Guangdong, China 电话 +86-769-2267 6998 Tel No.: 邮箱 info@waltek.com.cn Email: 网址 www.waltek.com.cn Website:
电池、电池组工厂名称及联系信息 Name and contact information of cell, battery Factory: 名称 珠海鹏远储能科技有限公司 Name: Zhuhai Pengyuan Energy Storage Technology Co.,Ltd 地址 珠海市金湾区红旗镇创兴中路 22 号厂房(一)、厂 Address: 房(二) Factory Building (1), Factory Building (2), No.22 Chuangxing Middle Road, Hongqi Town, Jinwan District, Zhuhai 电话 13556089768 Tel No.: 邮箱 liyongchun@seawitsin.ltd Email: 网址 / Website:	唯一的试验报告识别号码 A unique test report identification number: WTX24D06142752B001 测试报告签发日期 Issue date of the test report: 2024-07-25 参考所使用的《试验和标准手册》第 7 版修订 1 Reference to the revised edition of the Manual of Test and Criteria used: Rev.7/Amend1 试验结果表 List of tests conducted and results: 高度模拟 Altitude Simulation Pass 热测试 Thermal Test Pass 振动 Vibration Pass 冲击 Shock Pass 外部短路 External short circuit Pass ☒ 撞击/ Impact ☐ 挤压/Crush Pass 过充电 Overcharge Pass 强制放电 Forced discharge Pass
签字人姓名和职务 Name and Title of Signatory:  秦林伟 Deval Qin / 授权签字人 Designated Reviewer 签发日期 Issue Date: 2024-07-25	