




Special features

- Suitable for GU10/GU5.3 holders (sold separately)
- Lamps are easy to install thanks to the click lock

Housing Material	Metal
Housing Color	Silver
Housing Surface	Shiny
Dimmable	Yes
Control	Dimmable via optional light source
Motion Detector	No
Execution	Without lamp
Swivel Angle	30 Degree
Light Exit Surfaces	1
Light characteristics	Direct
Light direction	Below
Height	23 mm
Diameter	82 mm
Cut Out Diameter	68 mm
Product weight	71 g