




Special features

- Suitable for GU10/GU5.3 sockets [sold separately]
- Lamps are easy to install due to click lock

Housing Material	Metal
Housing Color	Silver
Housing Surface	Brushed
Dimmable	Yes
Control	Dimmable via optional light source
Motion Detector	No
Execution	Without lamp
Swivel Angle	30 Degree
Light Exit Surfaces	1
Light characteristics	Direct
Light direction	Below
Length	85 mm
Width	85 mm
Height	23 mm
Cut Out Diameter	68 mm
Product weight	88 g