

**Special features**

- Suitable for GU10/GU5.3 sockets [sold separately]
- Lamps are easy to install due to click lock

|                              |                                    |
|------------------------------|------------------------------------|
| <b>Housing Material</b>      | Metal                              |
| <b>Housing Color</b>         | Black                              |
| <b>Housing Surface</b>       | Matt                               |
| <b>Dimmable</b>              | Yes                                |
| <b>Control</b>               | Dimmable via optional light source |
| <b>Motion Detector</b>       | No                                 |
| <b>Execution</b>             | Without lamp                       |
| <b>Swivel Angle</b>          | 30 Degree                          |
| <b>Light Exit Surfaces</b>   | 1                                  |
| <b>Light characteristics</b> | Direct                             |
| <b>Light direction</b>       | Below                              |
| <b>Length</b>                | 85 mm                              |
| <b>Width</b>                 | 85 mm                              |
| <b>Height</b>                | 23 mm                              |
| <b>Cut Out Diameter</b>      | 68 mm                              |
| <b>Product weight</b>        | 88 g                               |