



Special features

- Can be dimmed using DALI2/DALI1
- Can be dimmed using 0-10 V/1-10 V
- Can be dimmed using touch dimmer via 230 V push-button (iPush)
- New Intelli-Push function [shortcut synchronises all connected power supply units when needed]
- Power supply unit and PWM dimmer in one device
- Secured against short circuits and overloads
- Overheating protection

| | |
|----------------------------|--|
| Housing Material | Plastic |
| Housing Color | White |
| Operating Mode | Constant voltage |
| Protection Class | Protection class II/protective insulation |
| Power | 150 W |
| Output Voltage | 48 V/DC |
| Output Current | 0-3125 mA |
| Dimmable | Yes |
| Control | DALI 2 / DT6, 0-10 V, 1-10 V, Intelli Push-Dim |
| Number of Channels | 1 |
| Power Factor | 0.98 |
| Connection Type | Clamp |
| Inrush Current max. | 38 A / 430 μ s |
| Reference Point Tc | 85 °C |
| Working Temperature | -20 to 50 °C |
| Storage Temperature | -40 to 85 °C |
| IP Protection Class | IP 20 |
| Switching Cycles | 25000 |
| Life Time | 50000 h |
| Length | 295 mm |
| Width | 40 mm |
| Height | 32 mm |
| Product weight | 417 g |

