



D-2/3A700 Specifications




Nominal Capacity	700mAh
Nominal Voltage	1.2V
Internal Impedance (at 1000Hz)	< 30mΩ
Charge	
Standard Charge	70mA x 15h
Rapid Charge	700mA x 1.2h
Discharge Cut-off Voltage	1.0V
Max Dimension (with tube)	
Diameter	17.0mm
Height	28.0mm
Weight	20 g
Operating Temperature	
Charge	0 ~ 45℃
Discharge	-20 ~ 60℃
Storage Temperature	
Within 1 month	-5 ~ 35℃
Within 6 months	0 ~ 35℃

Standard charge characteristics



Rapid charge characteristics



Discharge characteristics

