



D-1/2D2200 Specifications




Nominal Capacity	2200mAh
Nominal Voltage	1.2V
Internal Impedance (at 1000Hz)	<10mΩ
Charge	
Standard Charge	220mA x 15h
Rapid Charge	2200mA x1.2h
Discharge Cut-off Voltage	1.0V
Max Dimension (with tube)	
Diameter	33.0mm
Height	36.5mm
Weight	75 g
Operating Temperature	
Charge	0 ~ 45℃
Discharge	-20 ~ 60℃
Storage Temperature	
Within 1 month	-5 ~ 35℃
Within 6 months	0 ~ 35℃

Standard charge characteristics



Rapid charge characteristics



Discharge characteristics

