



ESG105RMCCFM - BATTERY-POWERED HYDRAULIC CUTTING TOOL

Klauke article number: ESG105RMCCFM

Short description

Remote-controlled cable cutter with max. 105 mm Ø cutting range, suitable for copper and aluminum cables

Scope of supply

- Battery-powered hydraulic cutting tool with max. 105 mm Ø cutting range
- Bluetooth remote control (BTC3)
- Ground adapter
- Fastening device
- Battery 18 V / 4.0 Ah, Li-Ion (RAL40)
- Quick-charger for 18 V Li-Ion batteries (LGL1)
- MK 105 L steel case (MK105L)

Features

- **Remote-controlled cable cutter**
- **Patented cutting blade end position detection** (the tool continuously checks the position of the blades. When the blades fully overlap, the tool gives out a visual and acoustic cutting confirmation from the remote control.)
- **Extremely long range** (up to 70m)
- **Ultra light design** (Thanks to its low weight (10.5 kg), the tool is very user-friendly)

Product data

International product number (GTIN) / EAN:	4012078965682
UPC:	-
Klauke article number:	ESG105RMCCFM
Special treatment class (hazardous material):	3481 (tool with Li-Ion battery)
Catchphrase:	Cu / Al – Cutter
Order unit:	1
Content unit:	1
Packaging volume:	1
Price unit:	1
Minimum quantity:	1
Gross weight:	21,200 kg
Net weight:	20,000 kg
Dimensions (LxBxH):	67,0 x 54,0 x 13,5 cm
Cutting force:	120 kN
Cutting area (diameter):	105 mm
Customs tariff number:	84672920
Warranty period (excl. blades):	2 years
Country of origin:	GE
Reach-conformity:	yes
RoHS-conformity:	yes
Certifications:	CE / IEC / VDE reg. F921 / MET / UKCA / GOST

