



EK WF 120 ML - BATTERY-POWERED HYDRAULIC CRIMPING TOOL

Klauke article number: EKWF120ML

Short description

BATTERY HYDRAULIC CRIMPING TOOL UP TO 120mm²

Scope of supply

- Battery-powered hydraulic crimping tool
- Battery 10,8 V / 1,5 Ah, Li-Ion (16,2 Wh) (RAML1)
- Charger for 10,8 V Li-Ion Battery, 230 V (LGML1)
- Plastic Case (KKML)



Features

- **Battery powered hydraulic crimping tool for wire ferrules, large cross-sectional area from 6 up to 120 mm²**
- **Only one crimping is necessary up to a wire end ferrule length of 32 mm**
- **Effortless operations thanks to low weight** (1.95 kg including battery)
- **Crimping of the common wire ferrules** according to DIN as well as insulated wire ferrules, twin wire ferrules and insulated twin wire ferrules
- **Slim crimping head** - ideal when space is critical
- **Manual retraction stop (MRS)**
- Closed head, rotatable
- Simple and safe: One-button operating concept for controlling all tool functions
- Ergonomic design for comfortable one-hand operation
- Powerful 10.8 V Li-Ion battery technology with battery charge indicator
- Fast crimping cycles for efficient work
- Rapid motor stop for high application safety
- Automatic retraction when operation is complete
- Manual retraction if necessary
- Maintenance display via LED
- Environmentally friendly hydraulic oil, rapidly biodegradable

product data

International product number (GTIN) / EAN:	4059577010161
UPC:	-
Klauke article number:	EKWF120ML
Special treatment class (hazardous material):	3481 (tool with Li-Ion battery)
Catchphrase:	Crimping tool
Order unit:	1
Content unit:	1
Packaging volume:	1
Price unit:	1
Minimum quantity:	1
Gross weight:	6,08 kg
Net weight:	1,96 kg
Dimensions (LxBxH):	44,0 x 41,0 x 11,0 cm
Crimping force:	10 - 40 kN
Crimping range:	6 - 120 mm ²
Ambient temperature:	-10 bis +40 °C
Customs tariff number:	84672920
Warranty period:	2 years
Country of origin:	GE
Reach-conformity:	yes
RoHS-conformity:	yes
Certifications:	CE / IEC / UKCA / GOST

