





THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE
UNIT: MM/IN X.
X.X

ISSUE NUMBER

ORIGINAL ①



SECTION A-A (1:1)

NOTES :

- 1.MATERIAL :TPU
- 2.DUROMETER: 75±5 A
- 3.DIMENSIONS:MM[INCHES]
- 4.TOLERANCE:±0.5[0.019]
- 5.USE CABLE TYPE RG59 OR RG62

PART NUMBER	COLOR	PACK
RG59/62SRB-B	BLUE	BULK
RG59/62SRB-G	GREEN	BULK
RG59/62SRB-R	RED	BULK
RG59/62SRB-Y	YELLOW	BULK
RG59/62SRB-BK	BLACK	BULK
RG59/62SRB-LG	LIGHT GREY	BULK

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

DRAWN Henry Pan		DATE 2023/03/03	
APPROVED Victor Lin		DATE 2023/03/03	
SCALE 1:1	SHEET OF 1 OF 1	REV: 1	
DRAWING No RG59/62SRB			



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2015/863/EU
AND 2011/65/EU FOR RoHS COMPLIANCY.



MH CONNECTORS ,
DIVISION OF EDAC