

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

MSK-122 rot MSK-122 sw TEST CLIP

CE


Item no. 3431133 (MSK-122 rot)

Item no. 3431134 (MSK-122 sw)

FEATURES

CAT II 1000V 5A // Socket 4 mm // Clip opening max. 6.5 mm

DIMENSIONS



All dimensions in mm

TECHNICAL DATA

Item	Value
Overvoltage category	CAT II 1000 V
Rated current	max. 5 A
Connection socket	4 mm
Clamp opening	max. 6.5 mm
Colour	Item 3431133 Red Item 3431134 Black
Tip material	Copper, carbon steel
Insulated material	PA
Operating condition	-5 to +45 °C, < 85% RH
Storage condition	-10 to +50 °C, < 85% RH
Dimensions	161 x 37.5 x 15 mm (L x H x W)
Weight	21 g

PACKAGE CONTENTS

8x Clips

