

Thermaltake CT120 ARGB PC Cooling Fan 2Pack

CT120 ARGB

PC Cooling Fan

2 Pack



TT thermaltake

REVISION A. 2022.12

Thermaltake CT120 ARGB PC Cooling Fan 2Pack

• Features

- Cable Integrated Daisy-chain Design with better cable management
- PWM Controlled Fan with a maximum speed of 2000 RPM
- 9 addressable LEDs controlled by 5V motherboard sync software
- Specifically tuned fan blade allows the air to be pushed further
- Optimized hydraulic bearing for reliable and silent operation
- Anti-vibration Mounting System Embedded

2 Pack

• Specification

Fan Dimension	120 x 120 x 25 mm
Started Voltage	5 V
Rated Voltage	12 V & 5V
Rated Current	0.11 A & 0.31A (one fan)
Power Input	1.32 W & 1.55W (one fan)
Fan Speed	PWM 500~2000 R.P.M
Max. Air Pressure.	2.23 mm-H2O
Max. Air Flow.	57.05 CFM
Noise Level.	25.8 dB-A
BeaRiing Type	Hydraulic Bearing
Life expectation	40,000 hrs,25°C
Connector	4 PIN PWM 3 PIN-ARGB
Note	PWM Cable x 2 ARGB Cable x2 ARGB Cable Clip x 2

Thermaltake CT120 ARGB PC Cooling Fan 2Pack

•Angle View



Front view



Back view



Cable Clip



Side view



Parts

(M3 for Radiator x 8, T5x10 fan screw x 8)
PWM extend cable*2, ARGB extend cable x2)



Application

Thermaltake CT120 ARGB PC Cooling Fan 2Pack

- Detail Features



Daisy-chain Design

better cable management



Anti-vibration mounting system

Reduce vibrations between fan and chassis



Application

To provide the best cooling solution inside your chassis

Thermaltake CT120 ARGB PC Cooling Fan 2Pack

CT120 ARGB PC Cooling Fan *2 Pack*



TT thermaltake