


DATASHEET

M8 60 V Angled plug, 3-pole, open end, 0.25 mm², black, 5 m

Item No. 3437963

Overview



Pin Assignment		
P1	Wire Color	OPEN
1	Brown	
3	Blue	
4	Black	

TECHNICAL REQUIREMENTS	
Coupling Type	Threaded connection
Termination Way	Soldering
Applicable temperature	-40 to +80 °C
Level of pollution	3
Protection Grade	IP67(Lock)
Durability	≥500
Rated voltage	60V AC/DC
Rated current	3A
Conductor impedance	≤5 mΩ
Insulation impedance	≥ 100 MΩ
Quality standards	IPC-A-620
ELECTRICAL CHARACTERISTICS	
High voltage test	DC 300V / 0.01S
Insulation impedance	10MΩ MIN
Conductor impedance	3Ω MAX
Open short test	100% TEST

- UL20549 3C*24AWG(7/0.2STC), inner core PVC,OD:1.1,Jacket
- 3 black fog surface (GS0827-ZC) 90A TPU polyether flame retardant FT2(coarse and sticky)(3C24-001)
- 2 M8 overmolding TPU black
- 1 CAZN M8 male plug semi-finished product 3core:M8-P3A-SFC

Dimensions in mm