
DATASHEET

M8 60 V plug, straight, 3-pole, IP67

Item No. 3438014

Overview



1	M8 Assembly connection screw	6	M8 Straight body plastic case
2	M8 Male Insulator 3 core A code ,black	7	Waterproof rubber plug Silicone Rubber black
3	Nitrile butadiene rubber ϕ10*ϕ8*1 black	8	Tail paw PA66 black
4	M8 Male contact pin Gold Plated OD:1.0	9	Lock cable nut, plastic case
5	Wire locking screw		

Technical specifications:		Materials:	
Coupling:	Threaded coupling	Shell material:	Nylon black
Termination:	Screw locking	Contact material:	Copper gold plated
Coding:	A	Insert material:	PA+GF UL94 black
Pollution degree:	3	Sealing:	NBR black
Temperature range:	−40 to +80°C		
Degree of protection:	IP67		
Mating cycles:	≥500		
Rated voltage:	60V AC/DC		
Rated current:	3A		
Contact resistance:	≤5 mΩ		
Insulation resistance:	≥100 MΩ		

Dimensions in mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.