

AQUAPIX®

W3027 wave



3 METERS
WATER
PROOF

Full HD
1920x1080

3M
WATERPROOF

5MP
SENSOR

30MP
MAX.
RESOLUTION

4X
DIGITAL
ZOOM

2.7"
6.8CM
DISPLAY

MICRO
SD CARDS
UP TO 128GB

ISO
400

LITHIUM
BATTERY
EXCHANGEABLE

W3027 WAVE

MARINE BLUE	ICEBLUE	PINK	YELLOW	SUNSET ORANGE
Art. 10034	Art. 10035	Art. 10033	Art. 10032	Art. 10031
4260041686458	4260041686779	4260041686793	4260041686786	4260041686441

WATERPROOF CAMERA

Waterproof housing	Up to 3m
--------------------	----------

RESOLUTIONS

Photo	30M* / 24M* / 20M* / 16M* / 12M* / 8M* / 7MHD* / 5M / 3M / 2MHD
Video	FHD* 1920x1080, HD 1280x720, VGA 640x480

DISPLAY

LCD display	2.7"/6.8cm
-------------	------------

FEATURES

Sensor	5MP
Digital zoom	4x
Lens	F/3.0 f=8.15mm
Focus range	1m ~ infinity
Exposure	-3.0EV - +3.0EV
Image Quality	Normal / Fine / Super Fine
Anti shake functon	Yes
Face detection	Yes
Scene mode	Auto, Scenery, Portrait, Night Scenery, Night Portrait, High Sensitivity, Sport, Beach, Party
Colour effects	Standard, Sepia, Monochrome, Vivid
Flash mode	Off, On, Auto, Red Eye Reduction
White balance	Auto / Daylight / Cloudy / Fluorescent / Incandescent
ISO	Auto / 100 / 200 / 400
File format	JPEG, AVI
Self-timer	2 sec / 5 sec / 10 sec
Auto Power Off	1 min / 3 min / 5 min
Interface	USB Type-C
Power source	650mAh lithium battery (exchangeable)
Dimensions	105 x 63 x 24 mm, 130g

EXTERNAL MEMORY (not included)

Compatible with microSD cards up to max. 128GB

INCLUDED

- Pouch
- Hand strap
- Lithium battery
- Usb cable
- Manual

* by interpolation

AQUAPIX®
W3027 wave



MARINE BLUE



ICEBLUE



PINK



YELLOW



SUNSET ORANGE