

DATASHEET

DC Power Cord with Battery Connector for Portable Fridge, 12/24VDC, 10 A

Item No. 3440807



Technical data

Rated Voltage	12/24V/DC
Rated Current	10 A
Contact Resistance	<10 mΩ
Insulation Resistance	>500 MΩ
Cable Size	1.31mm ² (AWG16)
Cable Length	1800 mm
Flame Retardant Grade	UL94V-0
Operating Temperature	-10°C ~ 105°C

Material

a) Battery Modular Connector

Hosing	Polycarbonate (PC)
Terminal Contact	Tin Plated Copper

b) 2 PIN DC Power Plug

Inner Insulation	LDPE
Outer Insulation	PVC
Contact	Copper

c) Cable

Conductor	Bare Copper
Insulation Jacket	PVC / VW-1

Dimensions

