

PET Braided Sleeving with Hook-and-Loop fastener Black Part-No.: 25CA479 ... 25C483



H&L-area width
↔



↔ Flat width

The flexible braided cable protection sleeve protects the contents and keeps things tidy with a simple and reliable principle. Thanks to the Hook-and-Loop fastener, even subsequent attachment is absolutely problem-free and can be removed very quickly.

Robust design - the tightly woven polyethylene terephthalate construction can withstand temperatures of up to 150 °C without compromising flexibility.

Bundling, labeling or protecting cables, wires and hoses is very simple and cost-effective. This flexible cable sleeve can also be used to protect against dirt, abrasion and animal bites. The cable(s) can be threaded through the Velcro side slit and can even be carried out on the move without restriction.

To prevent fraying, the sleeve should be cut with a hot cutting tool!

Technical data: Material: PET • Temperature range: -50 ... 150 °C • Color: black • RoHS compliant, REACH compliant, halogen free • Flammability class based on FMVSS 302, combustion rate ≤100 mm/min.

Part No.	Bundle ø max.	Bundle ø min.	Flat width	H&L-area width	Selling unit	GTIN	Complete reel content / max. length
25CA479	15 mm	13 mm	50 mm	10 mm	1 m +	4262511620726	25 m
25CA480	20 mm	18 mm	65 mm	10 mm	1 m +	4262511620733	25 m
25CA481	30 mm	22 mm	90 mm	20 mm	1 m +	4262511620740	25 m
25CA482	40 mm	30 mm	115 mm	20 mm	1 m +	4262511620757	25 m
25CA483	50 mm	33 mm	125 mm	20 mm	1 m +	4262511620764	25 m