

Hook-and-Loop Tape Roll Item-No.: 25CA508 ... 25CA525



Hook-and-loop-tape without buckles for flexible use and cutting. One side "Hook" / one side "Loop".

Technical data: Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: Black, White, Green, Yellow, Red, Blue • RoHS compliant, REACH compliant • 50 m per roll.

Part-No.	Description	Length	Width	Color	EAN/GTIN
25CA508	Hook-and-loop tape 50 m x 1 cm Black on Roll	50 m	1 cm	Black	4262511621013
25CA509	Hook-and-loop tape 50 m x 2 cm Black on Roll	50 m	2 cm	Black	4262511621020
25CA510	Hook-and-loop tape 50 m x 3 cm Black on Roll	50 m	3 cm	Black	4262511621037
25CA511	Hook-and-loop tape 50 m x 4 cm Black on Roll	50 m	4 cm	Black	4262511621044
25CA512	Hook-and-loop tape 50 m x 5 cm Black on Roll	50 m	5 cm	Black	4262511621051
25CA513	Hook-and-loop tape 50 m x 7,5 cm Black on Roll	50 m	7,5 cm	Black	4262511621068
25CA514	Hook-and-loop tape 50 m x 10 cm Black on Roll	50 m	10 cm	Black	4262511621075
25CA515	Hook-and-loop tape 50 m x 1 cm White on Roll	50 m	1 cm	White	4262511621082
25CA516	Hook-and-loop tape 50 m x 2 cm White on Roll	50 m	2 cm	White	4262511621099
25CA517	Hook-and-loop tape 50 m x 3 cm White on Roll	50 m	3 cm	White	4262511621105
25CA518	Hook-and-loop tape 50 m x 4 cm White on Roll	50 m	4 cm	White	4262511621112
25CA519	Hook-and-loop tape 50 m x 5 cm White on Roll	50 m	5 cm	White	4262511621129
25CA520	Hook-and-loop tape 50 m x 7,5 cm White on Roll	50 m	7,5 cm	White	4262511621136
25CA521	Hook-and-loop tape 50 m x 10 cm White on Roll	50 m	10 cm	White	4262511621143
25CA522	Hook-and-loop tape 50 m x 2 cm Green on Roll	50 m	2 cm	Green	4262511621150
25CA523	Hook-and-loop tape 50 m x 2 cm Red on Roll	50 m	2 cm	Red	4262511621167
25CA524	Hook-and-loop tape 50 m x 2 cm Yellow on Roll	50 m	2 cm	Yellow	4262511621174
25CA525	Hook-and-loop tape 50 m x 2 cm Blue on Roll	50 m	2 cm	Blue	4262511621181