

Wire ferrules / Twin-wire ferrules 0.5 mm² ... 10 mm² 100 pcs set



RoHS



REACH
Compliant



Quadrios wire end ferrules guarantee optimal crimp connections in conjunction with fitting crimping tools. This product series includes wire end ferrules with plastic collars as well as double wire end ferrules in all colors based on the DIN color code. The ferrules are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. Optimal for use with suitable wire end ferrule crimping pliers.

Technical data: Voltage (max.): 440 V, Material: polyamide (collar) / Material: copper • Cross-section: 0.14 mm² ... 10 mm² • Inner diameter: 0.7 mm ... 4.6 mm • AWG: 26 ... 7 • Color: DIN color code • Content: 100 pcs pack.

Part No.	Description	Cross-section	Barrel length	Color	Inner diameter	EAN	Content
25C533	Wire ferrules 0.14 mm ² , plastic-collar grey	0.14 mm ²	6 mm	Grey	0.7 mm	4262511621273	100 pcs
25C534	Wire ferrules 0.25 mm ² , plastic-collar yellow	0.25 mm ²	6 mm	Yellow	0.8 mm	4262511621280	100 pcs
25C535	Wire ferrules 0.34 mm ² , plastic-collar turquoise	0.34 mm ²	6 mm	Turquoise	0.8 mm	4262511621297	100 pcs
22C425	Wire ferrules 0.5 mm ² , plastic-collar white	0.5 mm ²	8 mm	White	1.1 mm	4260732280859	100 pcs
22C426	Wire ferrules 0.75 mm ² , plastic-collar grey	0.75 mm ²	8 mm	Grey	1.3 mm	4260732280866	100 pcs
22C427	Wire ferrules 1 mm ² , plastic-collar red	1 mm ²	8 mm	Red	1.5 mm	4260732280873	100 pcs
22C428	Wire ferrules 1.5 mm ² , plastic-collar black	1.5 mm ²	8 mm	Black	1.8 mm	4260732280880	100 pcs
22C429	Wire ferrules 2.5 mm ² , plastic-collar blue	2.5 mm ²	8 mm	Blue	2.3 mm	4260732280897	100 pcs
22C430	Wire ferrules 4 mm ² , plastic-collar grey	4 mm ²	9 mm	Grey	2.9 mm	4260732280903	100 pcs
22C431	Wire ferrules 6 mm ² , plastic-collar yellow	6 mm ²	12 mm	Yellow	3.6 mm	4260732280910	100 pcs
22C432	Wire ferrules 10 mm ² , plastic-collar red	10 mm ²	12 mm	Red	4.6 mm	4260732280927	100 pcs
22C433	Twin-Wire ferrules 0.5 mm ² , plastic-collar white	0.5 mm ²	8 mm	White	2x 1.1 mm	4260732280934	100 pcs
22C434	Twin-Wire ferrules 0.75 mm ² , plastic-collar grey	0.75 mm ²	8 mm	Grey	2x 1.3 mm	4260732280941	100 pcs
22C435	Twin-Wire ferrules 1 mm ² , plastic-collar red	1 mm ²	8 mm	Red	2x 1.5 mm	4260732280958	100 pcs
22C436	Twin-Wire ferrules 1.5 mm ² , plastic-collar black	1.5 mm ²	8 mm	Black	2x 1.8 mm	4260732280965	100 pcs
22C437	Twin-Wire ferrules 2.5 mm ² , plastic-collar blue	2.5 mm ²	10 mm	Blue	2x 2.3 mm	4260732280972	100 pcs
22C438	Twin-Wire ferrules 4 mm ² , plastic-collar grey	4 mm ²	12 mm	Grey	2x 2.9 mm	4260732280989	100 pcs
22C439	Twin-Wire ferrules 6 mm ² , plastic-collar yellow	6 mm ²	14 mm	Yellow	2x 3.6 mm	4260732280996	100 pcs
22C440	Twin-Wire ferrules 10 mm ² , plastic-collar red	10 mm ²	14 mm	Red	2x 4.6 mm	4260732281009	100 pcs

Connection only by qualified electricians!