

Heat-shrinkable-braided-sleeving with woven structure Item-No.: 25CA532 ... 25CA546



These shrink tube hose is perfect to protect wires, cables and tubing against environmental affect and provide a great look a t the same time!

Due to woven structure, this product does not provide water-protection but works fine against mechanic stress.

Technical data: Color: Black • Operating Temperature Range: -40 ... 125 °C • Recommended Shrink Temperature: 170 ... 200 °C (5 min.) • Minimum Shrink Temperature: 100 °C • Maximum Storage Temperature: 50 °C • Heat Shrink Ratio: 2:1 • Wall Thickness after Full-Recovery: appx. 1 mm • Longitudinal Change after Full-Recovery: -10 ... -20 % • Longitudinal Material: Polyester Fiber (PET) • Transverse Material: Irradiated Cross-linked, Modified Polyolefin (PE) • Coating Material: Modified Composite Acrylic • Selling unit: Roll or 1 m +.

Part-No.	Description	Pre-shrinkage inner ø	Post-shrinkage inner ø	Finished folded ø	EAN / GTIN	Length / comp. Roll
25CA532	Heat-shrinkable-braided-sleeving 6 mm Black Roll	6 mm	3 mm	12±3 mm	4262511621303	100m
25CA533	Heat-shrinkable-braided-sleeving 8 mm Black Roll	8 mm	4 mm	15±3 mm	4262511621310	100m
25CA534	Heat-shrinkable-braided-sleeving 10 mm Black Roll	10 mm	5 mm	19±3 mm	4262511621327	100m
25CA535	Heat-shrinkable-braided-sleeving 12 mm Black Roll	12 mm	6 mm	24±3 mm	4262511621334	100m
25CA536	Heat-shrinkable-braided-sleeving 16 mm Black Roll	16 mm	8 mm	29±3 mm	4262511621341	100m
25CA537	Heat-shrinkable-braided-sleeving 20 mm Black Roll	20 mm	10 mm	36±3 mm	4262511621358	100m
25CA538	Heat-shrinkable-braided-sleeving 25 mm Black Roll	25 mm	12.5 mm	44±3 mm	4262511621365	100m
25CA539	Heat-shrinkable-braided-sleeving 30 mm Black Roll	30 mm	15 mm	53±4 mm	4262511621372	50m
25CA540	Heat-shrinkable-braided-sleeving 35 mm Black Roll	35 mm	17.5 mm	60±4 mm	4262511621389	50m
25CA541	Heat-shrinkable-braided-sleeving 40 mm Black Roll	40 mm	20 mm	68±4 mm	4262511621396	50m
25CA542	Heat-shrinkable-braided-sleeving 50 mm Black Roll	50 mm	25 mm	85±5 mm	4262511621402	50m
25CA543	Heat-shrinkable-braided-sleeving 60 mm Black Roll	60 mm	30 mm	100±5 mm	4262511621419	50m
25CA544	Heat-shrinkable-braided-sleeving 70 mm Black Roll	70 mm	35 mm	116±5 mm	4262511621426	50m
25CA545	Heat-shrinkable-braided-sleeving 80 mm Black Roll	80 mm	40 mm	132±5 mm	4262511621433	50m
25CA546	Heat-shrinkable-braided-sleeving 90 mm Black Roll	90 mm	45 mm	145±5 mm	4262511621440	50m