

ESD Metal Wrist Strap Cord Set Part-No.: 25EC166



Features:

ESD Metal Wrist Strap, Press Stud, Grounding cable, Crocodile Clip and Banana Plug

Item No	Product Content
1903EC038	Metals Wrist Strap with a 10mm Stud, 1.8m Grounding Cable with a Banana Plug & additional Crocodile Clip

Specifications:

Inner band: Stainless Steel
 Back Plate: Stainless Steel
 Face Plate: Black Composite Plastic
 Cable style: Spiral, Black color
 Banana Jack: 4mm Barrel Type
 Crocodile Clip: 50mm Barrel Type

Application

Anti-static metal wrist strap sets are great personal grounding solutions. They should be securely attached either directly to the ground or via banana jack to an ESD table mat or ESD floor mat. Compatible with continuous monitors, table and floor mat grounds, as well as ESD bench grounds.

5 pcs ESD Brush Set Part-No.: 25EC166



	Length(cm)	Hairs Surface(cm)	Length of Hairs(cm)	Color
Brush 1	17.0	6.1 x 0.8	2.5	Black
Brush 2	14.3	4.7 x 0.8	2.5	Black
Brush 3	14.1	3.8 x 0.8	2.5	Black
Brush 4	14.8	1.8 x 0.8	1.8	Black
Brush 5	12.0	Φ1.1	1.6	Black

Characteristics:

Allow through cleaning of ESD sensitive assemblies without the danger of high charges generated by conventional brushes.

Handle: made of Conductive carbon loaded polypropylene.

Surface Resistance: $<10^5 \Omega$

Bristle Head: bristles made of polyamide.

Hair: Black colour, ~0.4 mm in diameter

Application: Clearing PCB, Surface of the Electronic Products.

5pcs ESD Plastic Tweezers Set Part-No.: 25EC166



Type	Length (mm)	Weight(g)	Gap Between Tips while Open(mm)
Straight Round Tips, 2mm wide	115	5	6.5
Straight Flat Tips, 6mm wide	115	4	12
Straight Flat Tips, 3mm wide	115	5	7
Bent pointed Tips	115	5	5
Straight pointed tips	115	4	6.5

Specifications:

Material: Conductive, Black Plastic

Electrostatic Dissipative, protects electronic components from static damage during precise operation

Anti-magnetic, Resistant to most Acids and other Corrosives.