

ESD Fabric Wrist Strap with Cord Set Part-No.: 25EC168



Features	Details
Termination Stud	Stud Size 10mm
Grounding Cable	Length 1800mm, Spiral cable Style, Covered with Non-Conductive PU Insulation
Crocodile Clip	Length 50mm, Jaw Opens 7.9 mm max.
Banana Plug	4 mm standard

Specifications:

Flexible

Reusable

Color: Light Blue

Suitable for Single Wire Use

Length: 200mm, Adjustable

Strap Thickness: 2mm

Weight: 10g

Material: PE mix

Resistance to the Grounding Point: unworn: <200Ω, worn on the wrist: 1 - 3 MΩ

5 pcs ESD Brush Set Part-No.: 25EC168



	Length(cm)	Hairs Surface(cm)	Length of Hairs(cm)	Color
Brush 1	17.0	6.1 x 0.8	2.5	Black
Brush 2	14.3	4.7 x 0.8	2.5	Black
Brush 3	14.1	3.8 x 0.8	2.5	Black
Brush 4	14.8	1.8 x 0.8	1.8	Black
Brush 5	12.0	Φ1.1	1.6	Black

Characteristics:

Allow through cleaning of ESD sensitive assemblies without the danger of high charges generated by conventional brushes.

Handle: made of Conductive carbon loaded polypropylene.

Surface Resistance: $<10^5 \Omega$

Bristle Head: bristles made of polyamide.

Hair: Black colour, ~0.4 mm in diameter

Application: Clearing PCB, Surface of the Electronic Products.

5pcs ESD Plastic Tweezers Set Part-No.: 25EC168



Type	Length (mm)	Weight(g)	Gap Between Tips while Open(mm)
Straight Round Tips, 2mm wide	115	5	6.5
Straight Flat Tips, 6mm wide	115	4	12
Straight Flat Tips, 3mm wide	115	5	7
Bent pointed Tips	115	5	5
Straight pointed tips	115	4	6.5

Specifications:

Material: Conductive, Black Plastic

Electrostatic Dissipative, protects electronic components from static damage during precise operation

Anti-magnetic, Resistant to most Acids and other Corrosives.