

5 pcs ESD Brush Set Part-No.: 25EC169



	Length(cm)	Hairs Surface(cm)	Length of Hairs(cm)	Color
Brush 1	17.0	6.1 x 0.8	2.5	Black
Brush 2	14.3	4.7 x 0.8	2.5	Black
Brush 3	14.1	3.8 x 0.8	2.5	Black
Brush 4	14.8	1.8 x 0.8	1.8	Black
Brush 5	12.0	Φ1.1	1.6	Black

Characteristics:

Allow through cleaning of ESD sensitive assemblies without the danger of high charges generated by conventional brushes.

Handle: made of Conductive carbon loaded polypropylene.

Surface Resistance: $<10^5 \Omega$

Bristle Head: bristles made of polyamide.

Hair: Black colour, ~0.4 mm in diameter

Application: Clearing PCB, Surface of the Electronic Products.

3 pcs ESD Brush Set Part-No.: 25EC169



	Length(cm)	Hairs Surface(cm)	Length of Hairs(cm)	Color
Large	22.5	9.5 x 2.2	2.2	Black
Medium	17.5	6.7 x 1.35	1.6	Black
Small	17.7	4.0 x 1.2	1.6	Black

Characteristics:

Allow through cleaning of ESD sensitive assemblies without the danger of high charges generated by conventional brushes.

Handle: made of Conductive carbon loaded polypropylene.
Surface Resistance: $<10^5 \Omega$

Bristle Head: bristles made of polyamide.
Hair: Black colour, ~ 0.4 mm in diameter

5pcs ESD Plastic Tweezers Set Part-No.: 25EC169



Type	Length (mm)	Weight(g)	Gap Between Tips while Open(mm)
Straight Round Tips, 2mm wide	115	5	6.5
Straight Flat Tips, 6mm wide	115	4	12
Straight Flat Tips, 3mm wide	115	5	7
Bent pointed Tips	115	5	5
Straight pointed tips	115	4	6.5

Specifications:

Material: Conductive, Black Plastic

Electrostatic Dissipative, protects electronic components from static damage during precise operation

Anti-magnetic, Resistant to most Acids and other Corrosives.