

ESD Grounding Cord Part-No.: 25EC171



Item No	Cable Length(mm)	Termination Type	Stud Size
1903EC014	3600	Banana plug & Alligator Clip	10 mm

Specifications:

Cable Style: Spiral cable

Wire Type: Single Wire

Color: Light Blue

Insulation: Polyurethane (Non-Conductive)

Use Type: Reusable

All the cables can withstand 1250 volts DC for at least one minute

Application:

ESD Grounding Cords shall be used to make electrical connections between groundable points and the ESD Grounding facility

**Unless otherwise noted, tolerance $\pm 10\%$*

Specifications and procedures subject to change without notice

ESD Fabric Wrist Straps Part-No.: 25EC171



Specifications:

Flexible
Reusable
Stud Size(mm): 10.0
Color: Light Blue
Suitable for Single Wire Use
Length: 200mm, Adjustable
Strap Thickness: 2mm
Weight: 10g
Material: PE mix
Protection Resistor: 1 MΩ

The High-Quality Elastic Anti-Allergic ESD Wrist Strap is Adjustable and Easy to Use. The Length Adjustment with Quick Release is Suitable for any Wrist. This Comfortable Wrist Band is Woven with Synthetic Fibers. It meets the Requirements of EN 61340-5-1

ESD Earth Bonding Plugs Part-No.: 25EC171



1903EC052

Item Number	Description	Sockets
1903EC052	Main bonding by EU plug	3 x 10 mm studs

Specifications:

Material: ABS

Color: Yellow

Size of Plug Casing: 51 x 49 x 31 mm

Weight: 36g



1903EC100

ESD Stud and Socket Adaptor for Banana Plugs

Length: 30 mm

Material: Brass with Nickel plating



Ideal for use on the bench or with earth bonding plugs in the factory and in the field