

Ampure Go™

Portable Electric Vehicle Cordset



Key Features

- State-of-the-art safety features with 4 temperature sensors to safeguard against overheating the household plug
- Compact, portable, 13A @230V
- 3 LED status bar
- IP67 Rated IC-CPD can be submerged up to 1m
- CE declaration of conformity
- Optional 32A high power plug as additional purchase
- Easy to use, simply plug-in and charge
- Type 2 coupler which is applicable for all vehicles meeting EU standards
- Easily mount in your garage or on a wall with the included bracket

Technical Specifications

Max Current	230V @ 13A (3kW)
System Package	320 x 320 x 100 mm
AC Compatibility	85 - 265 VAC, 45 - 65 Hz
Plug Type	E/F
Cable Length	6m
Weight	4.1 kg - module
Operating Temperature	-30°C to +50°C
Ingress Protection	IP67
Certified Altitude	4000m
Vehicle Connector	Type 2
Certification	IEC 62752
HMI	3 LED Status Bar

