Busbar 600 A with cover



Busbar 600 A 2P with 6 stud terminals, with cover




Busbar 600 A 2P with 6 stud terminals, without cover





Cover, with datasheet


Technical Specifications

Busbar 600 A with cover	
Max. current rating:	600 A
Max. Voltage rating:	52 VDC or 300 VAC
Terminal diameter:	M8/8mm
Terminal height:	28mm
Terminal material:	Stainless steel
Hex nut material:	Stainless steel
Recommended torque:	7 N·m
Terminals Screw:	M10/10mm
Terminals material:	Stainless steel
Busbar strip material:	Tin-plated copper (20 x 25 mm)
Base material:	ABS, black
Cover material:	Clear Polycarbonate
Weight:	1.48 kg
Dimensions (hxwxd) (with cover):	282 x 34 x 71 mm









Busbar 600 A 2P with 6 stud terminals and cover
（05-052030-11）