

Oclip Ultra

MINI MASTERPIECE



FLOOD LIGHT MAX OUTPUT	FLOOD LIGHT MAX THROW	SPOT LIGHT MAX OUTPUT	SPOT LIGHT MAX THROW	UV LIGHT MAX OUTPUT	MOONLIGHT MAX RUNTIME
530 Lumens	45 Meters	450 Lumens	130 Meters	800 mW	144 Hours

*This information is for market reference only. Please do not make it public.



▲ Olive Green



▲ Navy Blue

MARKET APPLICATIONS

Everyday Carry, Home Use, DIY, Repair

UPC : 6977261691985 (Olive Green)
6977261692364 (Navy Blue)

DESCRIPTION

Designed for ultimate convenience, Oclip Ultra is a compact yet powerful EDC mini light that seamlessly integrates into your daily routine. It features three essential light sources—a floodlight for wide-area illumination, a spotlight for long-range visibility, and a UV light for specialized inspections—ensuring you're prepared for any situation.

Built with OAL™—Olight's exclusive aluminum alloy, which is nearly twice as hard as 6061 aluminum—Oclip Ultra offers superior durability that stands the test of time. Its versatile carry options let you clip, magnetically attach, hang, or even pair it with a headband (optional), making it effortlessly adaptable to your needs.

With a clip tested for 10,000 uses, a patented hinged dust cover that withstands 3,000 cycles, and IPX6 water resistance—even with the cover open—Oclip Ultra takes versatility and durability to the next level.



FEATURE

- **Ultimate 3-in-1 Lighting:** A 530lm floodlight for wide-area illumination, a 130m spotlight for long-range visibility, and an 800mW pure 365nm UV light for specialized inspections—ready for any situation.
- **Ultra-Durable OAL™ Material:** Built with OAL™—Olight's exclusive aluminum alloy, nearly twice as hard as 6061 aluminum—for unmatched durability.
- **Versatile Clip-On Convenience:** Clip, magnetically attach, hang, or pair with a headband (optional)—effortlessly adaptable to your needs.
- **Ultimate Portability:** Mini form, maximum convenience. Ready when you need it, invisible when you don't.
- **Effortless Light Switching:** Instantly toggle between modes with an intuitive selector for quick, precise adjustments.
- **Pure 365nm UV Light:** A high-purity UV beam for detecting counterfeit currency, minerals, and cleanliness checks.
- **Sleek & Modern Aesthetic:** A timeless design blending a classic vibe with a futuristic edge.

SPECIFICATIONS

Floodlight					
SPECIFICATIONS	Turbo	High	Medium	Low	Moon
	530-300-100 lumens	300-180-100 lumens	100 lumens	10 lumens	1 lumen
	1+50+30 minutes	10+80+20 minutes	3.5 hours	27 hours	144 hours
	45 meters	34 meters	19 meters	6 meters	N/A
	505 cd	289 cd	91 cd	9 cd	N/A
	White Strobe: 13Hz@530lm/2h Signal Strobe: 0.33Hz@530lm/22h				
Spotlight					
SPECIFICATIONS	Turbo	High	Medium	Low	Moon
	450-270-90 lumens	270-160-90 lumens	90 lumens	9 lumens	1 lumen
	1+50+30 minutes	10+80+20 minutes	3.5 hours	27 hours	144 hours
	130 meters	100 meters	58 meters	18 meters	N/A
	4,225 cd	2,500 cd	840 cd	81 cd	N/A
	White Strobe: 13Hz@450lm/2h Signal Strobe: 0.33Hz@450lm/22h				
UV Light					
Output: 800~300mW		Max Runtime: 3+130min		Wavelength: 365~370nm	

* All data above are test results according to ANSI/NEMA FL 1-2019 standards.

LIGHT SOURCES

Floodlight LED: CCT: 5700~6500K, CRI: 70;
Spotlight LED: CCT: 5700~7000K, CRI: 70;
UV Light LED: Wavelength: 365~370nm;

DIMENSIONS

Width: 1.11 in/28.3 mm
Length: 2.24 in/57 mm
Thickness: 1.10 in/27.9 mm

WEIGHT

1.94 oz/55 g (Including Battery)

BODY MATERIAL

OAL™(O-Aluminum)

POWERED BY

580mAh Rechargeable Li-ion Battery, 3.7V

WARRANTY

Lifetime Warranty in Australia, China, France, Germany, and the USA. 2-Year Warranty in Other Countries and Regions.
Visit: <https://www.oight.com/lifetime-warranty>

IN THE BOX

Oclip Ultra x 1
USB-C Charging Cable x 1
Manual x 1

WATERPROOF IPX6



DROP TEST



COMPLIANCE



oight.com © Olight 26/03/25 V1
Made in China

Note: There are slight differences between the picture and the real item caused by light color temperature. All the pictures are for reference only.