

WARRIOR *Ultra*

A WARRIOR POET

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
2,500 lumens	55 days	320 meters

*This information is for market reference only. Please DO NOT make it public.



▲ Olive Green



▲ Navy Blue



▲ Stealth Grey

MARKET APPLICATIONS

Security
Law Enforcement
EDC
Search and Rescue

UPC

6977261691824 (Olive Green)
6977261692425 (Stealth Grey)
6977261691817 (Navy Blue)

DESCRIPTION

Designed for superior performance and built to last, the Warrior Ultra stands out with its premium O-aluminum construction, ensuring exceptional durability and wear resistance. Boasting an impressive 2,500-lumen output and 26,000 candelas on Turbo mode, it illuminates distances of up to 320 meters.

Powered by a high-capacity 5,000mAh 21700 lithium-ion battery, it offers an incredible runtime of up to 55 days in Moonlight mode. Engineered for tactical use, it features a jagged bezel for self-defense, a large, glove-friendly switch for effortless operation, and a knurled tail switch for a secure, comfortable grip. A built-in proximity sensor automatically dims the light when close to objects, preventing overheating or damage.

Whether for tactical missions or outdoor adventures, the Warrior Ultra delivers unmatched power, durability, and intuitive design to exceed expectations.



FEATURES

- **Premium Build Quality:** Crafted from O-aluminum, this flashlight is exceptionally durable, resisting wear to maintain its sleek appearance while protecting internal components.
- **True Tactical Performance:** With a powerful 2,500-lumen output and 26,000 candelas on Turbo mode, it illuminates distances of up to 320 meters.
- **High-Capacity 5,000mAh Battery:** Powered by a 21700 lithium-ion battery, it delivers an impressive runtime of up to 55 days in Moonlight mode.
- **Built for Tactical Use:** The jagged bezel not only enhances its aggressive design but also serves as a reliable self-defense tool and glass breaker.
- **Large, Easy-to-Find Switch:** The oversized switch allows quick, effortless operation—even in the dark or while wearing gloves.
- **Knurled Tail Switch:** Textured with raised dots, the tail switch provides a better grip, ensuring secure operation while offering a comfortable touch.
- **Auto-Dimming Proximity Sensor:** Automatically reduces brightness when near objects, preventing potential damage to both the flashlight and surrounding surfaces.

OUTPUT

SPECIFICATIONS	Turbo	High	Med	Low	Moonlight
	2,500 ± 800 ± 250 lumens	800 ± 250 lumens	200 lumens	15 lumens	1 lumen
	2.5+162+39 minutes	168+39 minutes	13 hours	130 hours	55 days
	320 meters	180 meters	95 meters	27 meters	6 meters
	26,000 cd	8,100 cd	2,300 cd	190 cd	9 cd

* All data above are test results according to ANSI/NEMA FL 1-2019 standards.

IP RATING IPX8



DROP TEST



COMPLIANCE



DIMENSIONS

1.14 x 5.51 in (29 x 140 mm)

WEIGHT

6.28 oz (178 g)

BODY MATERIAL

O-Aluminum

BATTERY

5000 mAh Lithium-ion Battery

WARRANTY

Lifetime Warranty in Australia, China, France, Germany and the USA.
5-Year Warranty in other countries and regions.

IN THE BOX

Warrior Ultra x 1
Flashlight Holster x 1
Magnetic Charging Cable x 1

OPTIONAL ACCESSORIES

sROD-7 Remote x 1
sROD Remote x 1
E-WM25 Flashlight Mount x 1