







ASSEMBLY




SECTION B-B




BOX - INSIDE




SECTION A-A



STEEL INNER PANEL



LID - INSIDE



SEE ENCLOSURE 1554XA
FOR MORE DETAIL

POLYCARBONATE
VERSION ONLY



NOTE

Purchased assembly includes box, lid, 6 cover screws, and preformed silicone gasket.
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)
Lid accepts 22.5mm push buttons

Recommended Cover screw torque -- 8-9 lbf-in (90-100 cN-m)

1554MPB	
1554MPB Enclosure	
Polycarbonate RAL-7035	1554MPB15A
ACCESSORIES	
Steel Inner Panels	1554XPL
Steel Panel / P.C. Board (Pkg 100) [M3-0.5 x 8mm Plated]	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#8 X 5/16" (8mm) Plated] (Pkg 100)	SC544-100
Cover Screws (Pkg 50) [M4-0.7 X 20mm Stainless Steel]	SC576-50



Dimensions:
mm
[inches]