



Mini-GBIC Single-Mode LC Module

TEG-MGBS10 (2.0R)

- Mini-GBIC module for single-mode fiber with an LC connector-type
- For distances up to 10km
- Designed to connect with a standard Mini-GBIC slot

The TEG-MGBS10 Mini-GBIC Single Mode module works with standard Mini-GBIC slots on most switches. This Single Mode LC Type module spans distances up to 10km (6.2 miles) and includes 1 x 1000Mbps-LX (LC-Type) Mini-GBIC connector.

- Compliant with IEEE 802.3z Gigabit Ethernet and Fiber Channel Standards
- Industry standard SFP package
- Duplex LC connector
- 1.0625Gbps Fiber Channel Compliant
- 1.25Gbps Gigabit Ethernet Compliant
- Single 3.3V Power Supply Voltage
- 3-year limited warranty

Specifications

Wavelength

- 1310nm

Optical Output Power (dBm)

- -9 ~ -3

Optical Input Power (dBm)

- -22 ~ -3

Power Budget

- -13

Distance

- 10km