



2-Port USB KVM Switch

TK-207K (v3.xR)

- 2-Port KVM switch with VGA and USB connections to computers
- High quality 2048 x 1536 resolution for a crisp display
- Control two computers with one set of console controls
- Device switching with auto-scan and audible feedback
- Supports most operating systems and advanced mouse designs
- Bus powered – No external power adapter required
- All required cabling included

TRENDnet's 2-Port USB KVM Switch, model TK-207K, allows you to manage two PCs with just one set of keyboard, monitor, and mouse. Switch between two PCs with a simple press of a button. Separate sets of KVM cables are included with the KVM Switch so that users can start controlling two PCs instantly. The KVM cables also provide power to the KVM Switch, eliminating the need for a power adapter. Hot Key operations provide immediate access to features, such as computer switching, and auto-scanning. With its hot key feature and audible feedback, the 2-Port USB KVM Switch is an ideal choice for managing multiple PCs.



VGA

Designed for VGA systems with resolutions up to 2048 x 1536 with a 60Hz refresh rate.



Push Button Controls

Use the front panel push buttons to easily switch between computers.



Included Cables

This KVM kit includes two sets of KVM cables.

FEATURES



Computers

Control up to 2 computers with one set of console devices



VGA

This VGA KVM switch supports resolutions up to 2048 x 1536 with a 60Hz refresh rate



Push Button Controls

Use the front panel push buttons on the KVM switch to easily switch between computers



Hot Keys

This VGA KVM switch features keyboard hot key commands for switching between computers



USB Mouse & Keyboard

Features USB keyboard and mouse connections



Included Cables

This KVM kit includes two sets of KVM cables



Computer Ports

Requires open USB and VGA ports from connected computers

NETWORKING SOLUTION



SPECIFICATIONS

Console Port Connectors

- 1 x VGA/SVGA HDB 15-pin (Female)
- 2 x USB 2.0 ports (Keyboard / Mouse)

Computer Interface (up to 2)

- 1 x USB 2.0 Type A
- 1 x VGA/SVGA HDB 15-pin (Female)

Cables (2 sets)

- Length: 1.2m (4 ft.)
- VGA/SVGA (Male) to VGA/SVGA (Male) / USB Type A

Monitor Resolution

- 2048 x 1536 @ 60Hz

Switching Control

- Front panel push buttons
- Keyboard hotkey commands

Operating Temperature

- 0° – 40° C (32° – 104° F)

Operating Humidity

- Max. 90% non-condensing

Power

- USB powered
- Max. consumption: 0.7W

Dimensions

- 95 x 63 x 24mm (3.74 x 2.48 x 0.95 in.)

Weight

- 96g (3.4 oz.)

Warranty

- 2-year

Certifications

- CE
- FCC

Package Contents

- TK-207K
- 2 x KVM cables (1.2m/4 ft.)

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.