

Wacom® Cintiq

Dive into Creativity



Wacom Cintiq is a creative pen display that comes with the industry-leading Wacom Pro Pen 3 that is also included with our professional models. With its ultra-responsive pen, high-resolution 2.5K display, and anti-glare surface, the Wacom Cintiq offers a natural, paper-like drawing experience across a spacious workspace. Choose the model that best fits your creative workflow: 16.0 in, 23.8 in, or 23.8 in with multi-touch.

Wacom Pro Pen 3 with improved drawing experience

The Wacom Pro Pen 3, which is also used in Wacom's flagship professional models, is included as standard. The battery-free pen does not require charging and delivers an accurate, sensitive, and natural drawing experience.



Compact design with a large active area High-resolution and high-quality display

The compact body features a fully flat, narrow bezel, along with a 2.5K resolution display, which is approximately 1.8 times greater than Full HD. The 23.8 in models offer a spacious drawing area and include a version with multi-touch, while the 16.0 in model has a reduced footprint that can fit on any desktop.



Easy connection and tidy cables for a clean creative workspace

Supports USB-C, HDMI*¹, and USB-A*¹ connectivity. The Wacom Cintiq 16 can be connected via a single USB-C cable*².



Wacom Adjustable stand Supports any angle that you like

The smooth and quiet adjustable stand lets you easily change the screen angle to match your posture and line of sight.



*¹ Requires HDMI to mini HDMI cable and USB-C to USB-A cable (sold separately).
*² Requires a computer that supports DisplayPort Alt Mode and USB Power Delivery.

Included with Cintiq 24 and Cintiq 24 touch, and also compatible with Cintiq 16 (sold separately).

Wacom® Cintiq

Model	 Wacom Cintiq 16	 Wacom Cintiq 24	 Wacom Cintiq 24 touch		
Model Number	DTK168	DTK246	DTH246		
Display Size / Resolution	16.0 in (40.6 cm) / WQXGA (2560 x 1600)	23.8 in (60.4 cm) / WQHD (2560 x 1440)			
Active Area	345 x 215 mm / 13.6 x 8.5 in	527 x 296 mm / 20.7 x 11.7 in			
Size	259 x 384 x 15 mm / 10.2 x 15.1 x 0.6 in	340 x 568 x 21 mm / 13.4 x 22.4 x 0.8 in			
Weight	2.0 kg / 4.5 lb	With stand: 5.7 kg / 13 lb	Without stand: 4.8 kg / 11 lb	With stand: 5.9 kg / 13 lb	Without stand: 5 kg / 11 lb
Color Performance	16.7 million (8bit x RGB = 24bit) DCI P3 99% (CIE1931) (typ), sRGB 100% (CIE1931) (typ)	16.7 million (8bit x RGB = 24bit) sRGB 100% (CIE1931) (typ)			
Viewing Angle	178 deg. (89/89) H / 178 deg. (89/89) V (typ)				
Contrast Ratio / Response Rate	1400:1 (typ) / 12ms (typ)	1000:1 (typ) / 12ms (typ)			
Input Power (Product Side)	DC 5V 3A : USB-C cable connection 9V 2.77A : USB-C cable + AC Power adapter connection	DC 20V 1.8A			
Aspect Ratio / Brightness	16:10 / 290cd/m² (typ)	16:9 / 350cd/m² (typ)			
I/O Connectors	1x HDMI Type-C (mini HDMI), 1x USB Type-C				
Graphics Input*1	USB-C port with DisplayPort™ Alt Mode, or HDMI port and USB port.				
Multi-Touch	No	No	Yes		
Pen	Battery-free Wacom Pro Pen 3 with 3 customizable side switches, 8,192 pressure levels. Not included: Customizable grip size, weight, and side switch parts.				
Support Pen Tilt Angle	60 degrees				
ExpressKey	No				
Stand	Built-in Stand: Yes Wacom Adjustable Stand: Accessory	Built-in Stand: No Wacom Adjustable Stand: Inbox			
Security	Kensington® Security Slot				
Compatibility / System Requirements	Windows 10 or later (latest service pack/build), macOS 13 or later, Android™ 8.0 and above*2. USB-C port with DisplayPort™ Alt Mode or HDMI™ and USB-A. Internet access to download driver and select downloadable software*3.				
What's Included	Wacom Cintiq 16, Wacom Pro Pen 3, Vari-angle Pen Stand (incl. 1 pc Standard Nib, 1 pc Felt Nib), Nib Remover, USB-C to C Cable (1.8M/DisplayPort Alt Mode), USB-C to C Cable (1.8M/Power), AC Power Adapter, AC Plug Head, Quick Start Guide, IPI sheet, IPI for Arabic (EMEA), Warranty card and QR code for Mainland China.	Wacom Cintiq 24 or 24 touch, Wacom Pro Pen 3, Vari-angle Pen Stand (incl. 1 pc Standard Nib, 1 pc Felt Nib), Nib Remover, USB-C to C Cable (1.8M/DisplayPort Alt Mode), AC Power Adapter, Power Cable (1.0M), Quick Start Guide, IPI sheet, IPI for Arabic (EMEA), Warranty card and QR code card for Mainland China.			
Optional Accessories	Wacom Pro Pen 3 (ACP50000DZ), Wacom Pro Pen 3 Straight Grip (ACK34801Z), Wacom Pro Pen 3 Flare Grip (ACK34802Z), Wacom Pro Pen 3 Wood Grip (ACK35304Z), Wacom Pro Pen 3E (ACP501E00DZ), Pen Tether for Pro Pen 3E (ACK42007K), Wacom Pro Pen 3 Standard Nibs (ACK24801Z), Wacom Pro Pen 3 Felt Nibs (ACK24819Z), Wacom Pro Pen 3 Rubber Nibs (ACK253010Z), Vari-angle Pen Stand (ACK45120Z), Wacom Adjustable Stand (ACK651KZ), USB-C to C Cable 1.8M (ACK4490601Z), HDMI to mini HDMI Cable 1.8M (ACK45106Z), USB-C to A Cable 1.8M (ACK4480601Z), ExpressKey Remote (ACK411050), Wacom Pro Pen 2 (KP-504E), Wacom Pro Pen slim (KP-301E), Wacom Pro Pen 3D (KP505), Pro Pen (KP-503E), Grip Pen (KP-501E), Classic Pen (KP-300E), Art Pen (KP-701E), Accessory Pen Black DTK-2451 / DTH-2452 (KP302E)				
	Power Adapter & Plug Head (ACK44914)	Power Adapter (ACK4481401Z), Power Cable 1.0M, C7 Type (ACK4480601)			

*1 To achieve the maximum resolution and refresh rate on Wacom Cintiq, the host PC ports need to support maximum resolution of product side and 60Hz. Thunderbolt 3 or later is also supported.
*2 Display mode requires manufacturer specific OS support. See Wacom support for display mode compatible devices.
*3 Wacom ID and product registration required. Agreement to Terms of Use and respective license agreement from bonus software companies required.

