

Product Specification PDF

Date	Correct as of 11th Jun 2025
Brand	C.K Tools
Product	T3200 01
Description	Vorteck Cobalt HSS Drill Bits Set
Barcode	5013969251357
Commodity code	8207509000
Country of origin	CN



Features & Benefits	~ Advanced Vortecck Tip Technology: Precision-engineered Vortecck tip technology revolutionizes the drilling process by breaking it down into multiple micro-cuts, efficiently dispersing swarf to enhance cutting speed and ensure a smoother operation. ~ Versatile Application: Designed for high-performance in tough materials such as high-strength steels, stainless steels, cast iron, as well as nonferrous metals, plastics, and wood, delivering exceptional versatility across demanding applications. ~ Self-Centring Precision: The innovative self-centring tip eliminates the need for pre-drilling or centre punching, even on challenging curved surfaces like pipes and conduit, ensuring accuracy and ease of use. ~ Burr-Free Precision Drilling: With an optimized tip and fully ground flute structure, this tool achieves clean, perfectly round holes with no burrs, meeting the highest standards of finish quality. ~ Enhanced Cutting Speed: Features an instant start and rapid entry design, enabling cutting speeds up to twice as fast as conventional drill bits for unmatched efficiency and productivity. ~ M35 Cobalt Construction: Constructed with high-grade M35 HSS with 5% Cobalt, these bits are engineered for superior heat dissipation, extending tool life and reducing the risk of burnout in heavy-duty applications. ~ Quick Lock Hex Shank: Equipped with a 6.3mm (¼") quick-lock hex shank, compatible with impact drivers and standard drill chucks, allowing for fast, secure bit changes and enhanced user convenience. ~ Durable Corrosion Protection: Finished with a premium black oxide coating and bronze finish, providing lasting corrosion resistance and a professional appearance.
---------------------	--

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	65	50
Width mm	-	160	22	570
Depth mm	-	115	19.5	24
Height mm	-	30	10	155
Weight	-	388	-	20100
Packaging Information	Card use	-	single sheet	double sheet
	Card gms	-	88	600
	Plastic use	-	-	-
	Plastic gms	-	-	-
	Metal use	mild steel	-	-
	Metal gms	28	-	-
	Timber use	-	-	-
	Timber gms	-	-	-