

Product Specification PDF

Date	Correct as of 11th Jun 2025
Brand	C.K Tools
Product	T3200 04
Description	Vorteck Cobalt HSS Drill Bits 4mm
Barcode	5013969251302
Commodity code	8207509000
Country of origin	CN



Features & Benefits	~ Advanced Vortek Tip Technology: Precision-engineered Vortek tip technology revolutionizes the drilling process by breaking it down into multiple micro-cuts, efficiently dispersing swarf to enhance cutting speed and ensure a smoother operation. ~ Versatile Application: Designed for high-performance in tough materials such as high-strength steels, stainless steels, cast iron, as well as nonferrous metals, plastics, and wood, delivering exceptional versatility across demanding applications. ~ Self-Centring Precision: The innovative self-centring tip eliminates the need for pre-drilling or centre punching, even on challenging curved surfaces like pipes and conduit, ensuring accuracy and ease of use. ~ Burr-Free Precision Drilling: With an optimized tip and fully ground flute structure, this tool achieves clean, perfectly round holes with no burrs, meeting the highest standards of finish quality. ~ Enhanced Cutting Speed: Features an instant start and rapid entry design, enabling cutting speeds up to twice as fast as conventional drill bits for unmatched efficiency and productivity. ~ M35 Cobalt Construction: Constructed with high-grade M35 HSS with 5% Cobalt, these bits are engineered for superior heat dissipation, extending tool life and reducing the risk of burnout in heavy-duty applications. ~ Quick Lock Hex Shank: Equipped with a 6.3mm (¼") quick-lock hex shank, compatible with impact drivers and standard drill chucks, allowing for fast, secure bit changes and enhanced user convenience. ~ Durable Corrosion Protection: Finished with a premium black oxide coating and bronze finish, providing lasting corrosion resistance and a professional appearance.
---------------------	---

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	65	250
Width mm	4	162	22	43
Depth mm	4	36	20.5	24
Height mm	70	12.3	10	21
Weight	9	15.5	1045	4705
Packaging Information	Card use	-	single sheet	double sheet
	Card gms	-	88	484
	Plastic use	-	-	-
	Plastic gms	6.5	-	-
	Metal use	-	-	-
	Metal gms	-	-	-
	Timber use	-	-	-
	Timber gms	-	-	-