

Product Specification PDF

Date	Correct as of 9th Jan 2025
Brand	C.K Tools
Product	T3213A
Description	Sheet Steel Holesaw Set 20, 25 & 32mm
Barcode	5013969251234
Commodity code	8207506000
Country of origin	TW



Features & Benefits	1/4" - 6.35mm hex quick lock shank compatible with impact drills ~ Flared collar prevents over drilling ~ Variable pitch teeth give reduced vibration and faster debris removal ~ slimline design reduces frictional heat build-up and prevents tooth burnout ~ 8% cobalt M42 steel increases durability and heat tolerance ~ Max 1.6mm sheet steel. ~ Contents: 20, 25 and 30mm
Health & Safety	Users and bystanders are advised to wear safety goggles
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	12	120
Width mm	77	85	155	430
Depth mm	32	35	80	290
Height mm	63	93	270	340
Weight	149	175	2150	22250
Packaging Information	Card use	single wall	double wall	carton
	Card gms	26	61	700
	Plastic use	FSC certafied cardboard box	0	-
	Plastic gms	1	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	-