

Product Specification PDF

Date	Correct as of 11th Jun 2025
Brand	C.K Tools
Product	T39077A 180-RND
Description	RedLine VDE Access Pliers 180mm
Barcode	5013969251883
Commodity code	8203200000
Country of origin	DE



Features & Benefits	~ Specially designed for electrical installation work where space is restricted ~ Lanyard ready REDLINE VDE Handles ~ Tapered nose - streamlined for better access, and ideal for gripping nuts and cutting wires in recessed cabinets ~ Gutter nut holder - specially profiled jaw for securely holding square nuts used on cable trays and cabinets ~ Pin holder - machined at 90° to the angled face for holding cable clips/nails upright while hammering ~ Two component, ergonomic design, with anti-slip horns for increased comfort, control & safety ~ Induction hardened jaws for outstanding long term performance ~ Cutting jaws with C.K optimised geometry for unsurpassed cutting performance ~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ VDE approved - individually tested to 10,000 V for safe live working up to 1,000 V ~ Conforms to VDE0682/201 - EN60900 ~ Cutting capacities: Hard: 1,6 mm / Medium hard: 2,5 mm / Soft: > 4,0 mm ~ Total length: 180 mm
Health & Safety	Users are advised to regularly examine their VDE tools, Even the slightest damage can compromise the insulation integrity and potentially expose the user to the risk of injury or even death
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	-	-
Width mm	60	71	-	-
Depth mm	23	33	-	-
Height mm	190	222	-	-
Weight	221	247	-	-
Packaging Information	Card use	Box	-	-
	Card gms	26	-	-
	Plastic use	-	-	-
	Plastic gms	-	-	-
	Metal use	-	-	-
	Metal gms	-	-	-
	Timber use	-	-	-
	Timber gms	-	-	-