

# Product Specification PDF

|                   |                                   |
|-------------------|-----------------------------------|
| Date              | Correct as of 30th Jun 2025       |
| Brand             | Kasp                              |
| Product           | K260190                           |
| Description       | 260 Disc Lock Hasp & Staple 190mm |
| Barcode           | 5013969902679                     |
| Commodity code    | 8302411000                        |
| Country of origin | CN                                |



|                     |                                                                                                                                                                                                                       |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Features & Benefits | ~ Hasp & Staple for Kasp Disc locks~ series K260 ~ Hardened staple ~ Zinc plated finish ~ Concealed fixings ~ Concealed hinge pins ~ Fixing screws included ~ Length: 190 mm ~ For maximal shackle diameter of: 13 mm |
| Warranty            | KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years. Fair wear and tear or Damage caused through inappropriate use or attempted break in is not covered.                        |

| Product Weights and Measures |              |                             |                     |                   |
|------------------------------|--------------|-----------------------------|---------------------|-------------------|
|                              | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
| Item Quantity                | 1            | 1                           | 6                   | 36                |
| Width mm                     | 55           | 60                          | 135                 | 360               |
| Depth mm                     | 190          | 130                         | 190                 | 490               |
| Height mm                    | 30           | 47                          | 105                 | 160               |
| Weight                       | 445          | 460                         | 2918                | 17.5              |
| Packaging Information        | Card use     | Boxed                       | Box                 | Case              |
|                              | Card gms     | 14                          | 86                  | 377               |
|                              | Plastic use  | Poly bag PE                 | 0                   | -                 |
|                              | Plastic gms  | 1                           | 0                   | 0                 |
|                              | Metal use    | 0                           | 0                   | -                 |
|                              | Metal gms    | 0                           | 0                   | 0                 |
|                              | Timber use   | 0                           | 0                   | -                 |
|                              | Timber gms   | 0                           | 0                   | 0                 |