



MAGNUS ONE EU27507TC (Windows)

SKU: ZBOX-EU27507TC-BE1/J/U/K/AUS-W4B, ZBOX-EU27507TC-BE-W5B

The MAGNUS ONE EU27507TC, at 8.48 liters, is the smallest desktop PC powered by a GeForce RTX 5070 Ti Graphics Card. Paired with the desktop Intel Core Ultra 7 Processor 265, the MAGNUS ONE EU27507TC excels at gaming, creative tasks, or powering AI experiences. Tool-less access mechanisms also make upgrading memory, storage, or even a new graphics card a breeze.



KEY FEATURES

- Powered by NVIDIA Blackwell architecture and DLSS 4
- Compact 8.48 Liter chassis
- Integrated 650W PSU
- Thunderbolt 4
- 20-core Desktop Intel Core Ultra 7 Processor 265
- Desktop GeForce RTX 5070 Ti 16GB GDDR7 GPU
- Native 4K output, up to 4 displays
- Real-time Ray Tracing
- DLSS 4 with Multi-Frame Generation
- NVIDIA® Studio Drivers Compatible
- NVIDIA® G-SYNC® compatible
- Microsoft DirectX 12
- Wi-Fi 7 & Bluetooth 5.4, Dual LAN (5Gbps + 1Gbps)
- Gaming Ready / Creator Ready / 4K Ready / AI Ready



DUAL LAN



THUNDERBOLT 4



WIFI 7



UHS-II SDXC CARD READER



ULTRA HD 4K



QUAD DISPLAY SUPPORT

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

- Intel Core Ultra 7 Processor 265 (20-core, 2.4 GHz up to 5.3 GHz)
- ZOTAC GAMING GeForce RTX 5070 Ti 16GB GDDR7 (Graphics card compatibility – Power: max 300W, Width: dual-slot, Length: max 245mm/9.65in)
- 650W PSU

DISPLAY OUTPUTS

- 1 x HDMI 2.0 (integrated)
- 3 x DisplayPort 2.1b with UHBR20 (up to 4K 480Hz or 8K 165Hz with DSC)
- 1 x HDMI® Connector (Supports 4K 480Hz HDR or 8K 120Hz HDR with DSC, and Gaming VRR as specified in the HDMI 2.1b Specification)
- DisplayPort via Thunderbolt 4 (integrated)
- Max 4 displays (cloned) or 6 displays (extended)

HARD DRIVE & MEMORY

- 16GB DDR5 SO-DIMM Memory (one out of two slot occupied, up to 96GB)
- 1 x 2.5-inch SATA III HDD/SSD bay
- 1TB M.2 NVMe PCIe 4.0 x4 SSD (Slot speed: PCIe 5.0 x4)
- 1 x M.2 NVMe PCIe 4.0 x4 SSD slot (2242/2280)

FRONT PORTS

- UHS-II 3-in-1 card reader (SD/SDHC/SDXC)
- 2 x USB 3.0 ports (1 Type-C)
- Power button and power LED
- Wi-Fi LED, Hard drive LED

REAR PORTS

- Power Connector
- 2 x USB 3.0 ports
- 4 x USB 3.2 GEN 2 ports
- 1 x 10/100/1000 Ethernet
- 1 x 10/100/1000/2500/5000 Ethernet
- Dual Wi-Fi antenna connector
- 1 x Thunderbolt 4 port

CONNECTIVITY

- Wi-Fi 7 (802.11 be)
- Bluetooth 5.4

AUDIO OUTPUTS

- Onboard 8 Channel Digital Audio via HDMI
- Analog Stereo In / Out

SOFTWARE COMPATIBILITY

- Microsoft Windows 11 Home Pre-installed*

INSIDE THE BOX

- ZOTAC ZBOX MAGNUS ONE EU27507TC with Windows 11
- Power Cord (bundled cable quantity and type dependent on region)
- 2 x Wi-Fi Antenna
- USB Flash Drive with OS recovery
- Quick Install Guide

MINI PC DIMENSIONS

- Length: 270.5mm (10.65in)
- Width: 126mm (4.96in)
- Height: 249mm (9.8in)

BOX DIMENSIONS

- Length: 440mm (17.32in)
- Width: 327mm (12.87in)
- Height: 205mm (8.07in)

*Windows 11 Home N for Regions of Europe.

©2025 ZOTAC Technology Pte. Ltd. All rights reserved. All company and/or product names may be trade names, trademarks and/or registered trademarks of the respective owners with which they are associated. Features, pricing, availability and specifications are subject to change without notice. ZOTAC Technology Pte. Ltd. does not warrant the accuracy, completeness or reliability of information, materials and other items contained on this website or server. No liability is assumed with respect to the use of the information contained herein. When accessing this website, users acknowledge that ZOTAC Technology Pte. Ltd. will not be liable in any event for any damages arising out of the use of this site or any websites linked to it.

©2025 NVIDIA Corporation. NVIDIA, the NVIDIA logo, and GeForce are registered trademarks of NVIDIA Corporation in the U.S. and other countries. All rights reserved.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc..

ZOTAC.COM